



More information on the website
radwag.com/en/info,w1,00T

DWT/HL HP Checkweigher

WK-102-____



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	7500 g
Readability [d]	0.2 g
Tare range	-7500 g
Physical parameters	
Display	12" graphic colour touchscreen
Environmental conditions	
Operating temperature	0 – +40 °C
Features of use	
Capacity	max 180 pcs/min
Speed	0.1 – 1 m/s



Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Keypad, external switches

USB adapter

Receipt Printer

USB cable (scale - printer)

Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]