


















More information on the website
radwag.com/us/info,w1,089

MYA 21.5Y.P Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Percent Weighing
-  Peak hold
-  Statistics
-  IR sensors
-  GLP Procedures
-  Pipettes Calibration
-  Air density correction
-  Moveable range
-  Differential weighing
-  Ambient conditions monitoring
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	21 g
Minimum load	0,1 mg
Readability [d]	1 µg
Verification unit [e]	1 mg
Tare range	-21 g
Standard repeatability [5% Max]	1 µg

Standard repeatability [Max]	3 µg
Standard minimum weight (USP)	2 mg
Standard minimum weight (U=1%, k=2)	0,2 mg
Permissible repeatability [5% Max]	1,6 µg
Permissible repeatability [Max]	4 µg
Linearity	±7 µg
Eccentric load deviation	7 µg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	~ 5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass vessel, evaporation ring, glass lid, additional glass lid, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø 90×90 mm
Capacity	11 ml
Weighing pan dimensions	ø26 mm
Packaging dimensions	750×492×595 mm
Net weight	9,1 kg
Gross weight	16,6 kg
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Operating temperature	
Operating temperature	+10 – +40 °C
Operating temperature change rate	
Operating temperature change rate	±0,3 °C / 1 h (±1 °C / 8 h)
Relative humidity	
Relative humidity	40% – 80%
Relative humidity change rate	
Relative humidity change rate	±1% / h (±4% / 8 h)

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration tables

Workstation for pipettes calibration
RS 232, RS 485 cables
Label Printers

Power Adapters
Additional modules
Anti-Draft Chamber for Microbalances
Automatic Variable-Volume Pipettes
Professional Weighing Tables
Antistatic ionizer
Protective cover for balances
Barcode scanners

THBR 2.0 System - Ambient Conditions Monitoring
RS 232, RS 485 cables
Chamber for filter weighing
Receipt Printer
Fingerprint Reader
Protective cover for balances
RS 232 – USB Converter

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- R-Pipettes [WX-010-0026]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

Device dimensions

