



# HX5.EX-1.4P2.4000.H1 Beam Scale

WW-009-0047

More information on the website  
[radwag.com/us/info,w1,09Q](http://radwag.com/us/info,w1,09Q)



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

## Datasheet

Maximum capacity [Max]	4000 kg
Minimum load	40 kg
Readability [d]	2000 g
Tare range	-4000 kg
OIML Class	III
<b>Physical parameters</b>	
Display	5" graphic colour

Physical parameters	
Cable length	3 m + 5 m
Weighing pan dimensions	2 pcs 2 m
Net weight	97,8 kg
Gross weight	98 kg
Construction	
Protection class	IP 66 / 69 construction, IP 66 / 68 terminal
ATEX Certification	II 2G Ex ib IIC T4 Gb II 2D Ex ib IIIC T135°C Db
IECEX Certification	Ex ib IIC T4 Gb Ex ib IIIC T135°C Db
Construction	Stainless steel AISI304
Communication interface	
Communication interface	2×RS232, RS485
Power supply	
Power supply	100 – 240 V AC 50/60 Hz
Power consumption max.	15 W
Operating temperature	
Operating temperature	-10 – +40 °C
Relative humidity	
Relative humidity	10% – 85% RH no condensation
Indicator	
Indicator	PUE HX5.EX-1



Additional fee for verification



## Accessories (Additional Fee)

Communication modules  
Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX  
Weighing Terminal

Receipt Printer

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]