



More information on the website  
[radwag.com/en/info,w1,0EC](http://radwag.com/en/info,w1,0EC)

# DWT/HL 1500 HP Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 g
Readability [d]	0.5 g
Tare range	-1500 g
Physical parameters	
Display	5.7" resistive colour touchscreen
Environmental conditions	
Operating temperature	0 ÷ +40 °C
Features of use	
Capacity	max 180 pcs/min
Speed	0.1-1 m/s



Extra payment for verification

## Accessories

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

Keypad, external switches

USB adapter

Receipt Printer

USB cable (scale - printer)

## Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]