



More information on the website
radwag.com/it/info,w1,0EW

Bilance di precisione 5Y.50.PM



The drawings, photos and graphics used are for illustrative purposes only.

funzioni



Autotest



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit
measurement



Statistics



Checkweighing



IR sensors



GLP Procedures



Animal weighing



Pipettes Calibration



Air density correction



Density determination



Differential weighing



Ambient conditions
monitoring



Statistical Quality Control



Packaged Goods Control



ALIBI Memory



Wi-Fi

Foglio di calcolo

Parametri metrologici

Capacità massima [Max] 50 kg

Pesata minima 5 g

Parametri metrologici	
Accuratezza	0,1 g
Intervallo di verifica della bilancia [e]	1 g
Intervallo di tara	-50 kg
Pesata minima (secondo USP)	82 g
Pesata minima (U=1%,k=2)	8,2 g
Ripetibilità (Max)	0,15 g
Ripetibilità (5% Max)	0,04 g
Linearità	±0,3 g
Tempo di stabilizzazione	1 s
Calibrazione	internal (automatic)
Classe OIML	II
Parametri fisici	
Sistema di livellamento	semi-automatic - LevelSENSING
Display	10" graphic colour touchscreen
Dimensioni del piatto di pesata	350×260 mm
Dimensioni del pacco	520×520×280 mm
Peso netto	12 kg
Peso lordo	14,2 kg
Costruzione	
Punteggio IP	IP 43
Interfaccia di comunicazione	
Interfaccia	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Parametri elettrici	
Alimentatore	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 16V DC 1,4A max*
Environmental conditions	
Temperatura di lavoro	+10 – +40 °C

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessori

MediaBox
Tag RFID
Tavoli antivibranti
Alimentatore
Moduli aggiuntivi
Tavolo di pesata professionale
Capottina protettiva per bilance
Lettore di codici a barre

Contenitore per stoccaggio bilance
Under-pan weighing
Cavo seriale RS 232, RS 485
Cavo seriale RS 232, RS 485
Supporto, set di montaggio a muro e braccetti di montaggio
Stampanti di ricevuta
Lettore di impronte digitali
RS 232 – USB Converter

Software

- E2R Weighing [WX-010-0099]
- Editore di etichette R02 [WX-010-0094]
- Editore per sistemi di pesatura 2.1 [WX-010-0173]
- E2R Weighing Records [WX-010-0038]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions

