



More information on the website
radwag.com/en/info,w1,0LN

TM-U220A Epson Printer



The drawings, photos and graphics used are for illustrative purposes only.

Overview

This is the first receipt printer of RADWAG production.

We offer two models which differ in terms of communication interfaces:

RTP-RU80 – RS 232* and USB, RTP-UEW80 – USB, Ethernet and Wi-Fi. The printers communicate with all RADWAG laboratory balances and industry scales. Their connection and configuration is intuitively easy and takes barely few moments (Plug and Play). Communication via Wi-Fi enables remote printing. The printers are equipped with a paper cutter ensuring operation ergonomics.

The set includes: RTP-RU80: printer; power supply; cable with a plug of European standard, type C or E/F; USB cable; RS232 cable, female/ male; 80 mm thermal paper, 1 roll; RTP-UEW80: printer; power supply; cable with a plug of European standard, type C or E/F; USB cable; 80 mm thermal paper, 1 roll.

*RS 232 port comes in a female version

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Compatible with

H315 HR Waterproof Platform Scale
MA X7.IC.A Moisture Analyzer
DWT/HL/HP Checkweighers
MUYA Modules
MAS1 Modules
WPY Multifunctional Scale
Microbalance for Pipette Calibration MYA 5Y.P
HY10.HRP.H Stainless steel High Resolution Scale
MA 5Y Moisture Analyzer
C315 Platform scale
Microbalance for Filters MYA 5Y.F
TMX H Stainless steel Multifunctional Scale
RS 232 cables (scale - printer)
WLY Scales for PGC
MA X2.IC.A Moisture Analyzer
AS X7 Analytical Balance
PS X2 Precision Balance
AS X2 PLUS Analytical Balance
TMX Multifunctional Scale
C315.D Baby Scale
WLC Precision Balance
PS R2 Precision Balance
C315.4P2 Beam Scales
WLC X2 Precision Balance
H315 4H Stainless Steel Platform Scale
H315 4P2.H Stainless steel Beam Scales
WLC X7 Precision Balance
PS X2 Balances for PGC
DWT/RC/HYF Checkweighers
H315 H Waterproof Platform Scale
MA X2.A Moisture Analyzer
HY10 Multifunctional Scale
PUE 5 Weighing Terminal
MAS Modules
HY10 H Stainless Steel Multifunctional Scale
H315.4 H/Z Stainless Steel Platform Scale, pit version
MPS Modules
H315 4N.H Stainless Steel Ramp Scale
PUE 7.1.HRP High Resolution Scale
C315.4 Platform Scale
HY10.HRP High Resolution Scale
C32.PM Precision Balance
MA X7.A Moisture Analyzer
C315.O Personal Scale
H315 4N.H.LD Stainless Steel Ramp Scale
PS X7 Precision Balance
WPY Scales for PGC
C315.4P pallet scales
WAY 5Y.KO Manual Mass Comparator

MA 5Y.IC Moisture Analyzer
MA R Moisture Analyzer
AS 5Y Analytical Balance
AK-4 Automatic Mass Comparator
AKM-2 Automatic Mass Comparator
PS R2.H Precision Balance
HY10.H Scales for PGC
WTC Precision Balance
Dust-Free Cabinets for Printers
H315 4C Platform Scale
C315.OW Personal Scale
XA 5Y.F Analytical Balance for Filters
WLY Precision Balance
UMA Automatic Mass Comparator
H315 2K Overhead Track Scales
APP 5Y.KO Manual Mass Comparator
H315 4P.H Stainless Steel Pallet Scales
Robotic Mass Comparators
Density Measurement
WLC C/2 Precision Balance
H315 4I.S Livestock Scales
PS R1 Precision Balance
MA X2.A Moisture Analyzers
5Y.PM.KB Manual Mass Comparator
AS R2 PLUS Analytical Balance
PUE 7.1 Weighing Terminal
DWT/HL/HPW Checkweighers
PS 5Y Precision Balance
Postal Scales for Packages
DWR/H Checkweighers
Automatic Vacuum Mass Comparators
PMV 5Y Moisture Analyzer
XA 5Y.KO Manual Mass Comparator
H315 4I.H Stainless Steel Livestock Scales
PUE C315 Weighing Terminal
UYA 5Y.KO Manual Mass Comparator
AS R1 PLUS Analytical Balances
DWM H2 Checkweighers
C315.4B Bed Scale
PUE H315 Weighing Terminal
Nano-Comparator NANO.AK-4.500.5Y
DWM Checkweighers
DWT/RC/HY Checkweighers
C315.K Chair Scale
Roller Scales
DWT/HL/HPC Checkweighers
H315 Stainless Steel Overhead Track Scales
C315.8B Ramps Bed Scale