



More information on the website
radwag.com/en/info,w1,0PE

MA 210.X2.IC.A.WH Moisture Analyzer



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Statistics
-  IR sensors
-  GLP Procedures
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Drying modes
-  Samples drying
-  Moisture content analysis
-  Dry mass determination
-  Wi-Fi

Datasheet

| Metrological parameters | |
|--------------------------------|---|
| Maximum capacity [Max] | 210 g |
| Readability [d] | 1 mg |
| Tare range | -210 g |
| Adjustment | internal (automatic) |
| Maximum sample weight | 210 g |
| Heating module | halogen |
| Moisture content repeatability | +/-0.05% (sample ~ 2g), +/-0.01% (sample ~ 10g) |

| Metrological parameters | |
|-------------------------------------|--|
| Moisture content readability | 0.001% |
| Drying temperature range | Max 250 °C |
| Physical parameters | |
| Leveling system | manualny |
| Display | 5" graphic color touchscreen |
| Weighing chamber | automatic |
| Maximum sample height | 20 mm |
| Weighing pan dimensions | ø90, h= 8 mm |
| Packaging dimensions | 476×381×346 mm |
| Net weight | 5.4 kg |
| Gross weight | 6.9 kg |
| Construction | |
| Protection class | IP 43 |
| Features of use | |
| Display mode | %MC, %DC, %ATRO MC, %ATRO DC, g, g/kg MC, g/kg DC, -%MC |
| Drying method | 4 drying profiles (standard, fast, step, mild) |
| Finish mode | 4 modes (automatic, manual, time-defined, user-defined) |
| Additional functions | sample traceability |
| Communication interface | |
| Communication interface | RS232 ¹ , USB-A, USB-B, Ethernet, Wi-Fi |
| Electrical parameters | |
| Power supply | 100V – 120V AC 50/60Hz or 200V-240V AC 50/60Hz |
| Power consumption | 6 W |
| Heating module power | 450 W |
| Environmental conditions | |
| Operating temperature | +10 ÷ +40 °C |
| SOP – metrological tests | |
| Mass indication control | External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer) |
| Mass indication control | External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer) |
| Internal adjustment | For .IC models only, GLP report |
| External adjustment | For all models, GLP report |
| Drying temperature control | One- or two-point, depending on the drying profile (equipment: GT105k-12/Z Control Thermometer) |
| Moisture content indication control | Certified MV Test Set |
| Adjustment | |
| Internal / External adjustment | Depending on the type of moisture analyzer, GLP report |
| Drying temperature adjustment | Three-point adjustment at defined temperatures, programmable values (equipment: GT105k-12/Z Control Thermometer) |

¹ Barcode scanners, available as weighing instrument accessory, communicate with the instrument via RS232 interface exclusively.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

Antivibration Tables
Moisture analyzer accessories
Barcode scanners
Receipt Printer
Protective cover for balances

RS 232, RS 485 cables
Additional modules
RS 232 cables (scale - printer)
RS 232 – RS 485 Converter

Software

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]

- E2R Moisture Analyzers [WX-010-0072]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions

