



More information on the website
radwag.com/en/info,w1,0XU

CK-02/3 Transponder Card Reader



The drawings, photos and graphics used are for illustrative purposes only.

Overview

Transponder card reader is used for quick identification and logging of operators to a weighing system or identification of vehicles on a weighbridge. CK-02/3 is designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal. Area of Use: Additional equipment of load cell based industrial scales; Identification of weighing instrument operator; Identification of vehicles on weighbridges. Design: Transponder card reader CK-02 is manufactured in plastic housing. Intended Use: Designed for scales equipped with terminals PUE C41H and PUE 5 series. It is installed next to the terminal. Communication through RS 232, power supply 5V from scale terminal.

Compatible with

HY10.HRP.H Stainless steel High Resolution Scale
 TMX H Stainless steel Multifunctional Scale
 TMX Multifunctional Scale
 DWT/RC/HYF Checkweighers
 HY10 Multifunctional Scale
 HY10 H Stainless Steel Multifunctional Scale
 PUE 7.1.HRP High Resolution Scale

HY10.HRP High Resolution Scale
 HY10.H Scales for PGC
 Rotational Control Scales
 PUE 5 Weighing Terminal
 H315 H Waterproof Platform Scale
 Control Scales for Large Loads