



More information on the website
radwag.com/en/info,w1,13F

C315.60/150.OR-3 Personal Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Internal battery



Peak hold



GLP Procedures



ALIBI Memory



BMI

Datasheet

Metrological parameters	
Maximum capacity [Max]	60 / 150 kg
Readability [d]	20 / 50 g
Tare range	-150 kg
OIML Class	III
Physical parameters	
Display	LCD (backlit)
Communication interface	
Communication interface	RS232

Communication interface	
Optional interfaces	RS232
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz and battery
Power consumption max.	5 W
Operation time on batteries	up to 8 h
Environmental conditions	
Operating temperature	0 ÷ +40 °C
Relative humidity	10% ÷ 85% RH no condensation



Extra payment for verification

Accessories

RS 232 cables (scale - printer)
Cigarette lighter receptacle power supply cables
Displays
Displays
RS 232, RS 485 cables
RS 232 – Ethernet Converter


AP2-1 Current Loop Unit
RS 232, RS 485 cables
RS 232 – USB Converter
RS 232 cables (scale - printer)
RS 232 – RS 485 Converter
Receipt Printer

Software



- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]

- R-Panel [WX-010-0187]
- Scale Editor 2.1 [WX-010-0173]




Device dimensions



C315.OW



C315.OR



C315.OK