



More information on the website  
[radwag.com/us/info,w1,13S](http://radwag.com/us/info,w1,13S)

# DWT/RC 60/HYF Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Maximum capacity [Max]	60 kg
Minimum load	400 g
Readability [d]	20 g
Tare range	-60 kg
<b>Physical parameters</b>	
Display	10" graphic colour touchscreen
Weighing platform height	800 ±50 mm (other levels of platform on client requirement)
<b>Construction</b>	
Protection class	IP 66/67
Operating temperature	-10 ÷ +40 °C
<b>Features of use</b>	
Conveyor velocity	0,1 - 0,5 m/s



## Accessories

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

## Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]