



# High Resolution Platforms PL.300.1.HRP.H

WX-009-0159

More information on the website  
[radwag.com/en/info,w1,142](http://radwag.com/en/info,w1,142)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	300 kg
Preload range	60 kg
Readability [d]	1 g
Tare range	-300 kg
Repeatability	3 g
Linearity	±6 g
Adjustment	internal (automatic)
Construction	
Protection class	IP 66 / 67
Construction	Stainless steel AISI304
Weighing pan material	Stainless steel AISI304
Communication interface	
Communication interface	RS232, RS485, Ethernet

Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	+10 – +40 °C
Relative humidity	15% – 80%
Physical parameters	
Weighing pan dimensions	1000×800 mm
Packaging dimensions	1000×1200×436 mm
Net weight	126 kg
Gross weight	160 kg



## Accessories (Additional Fee)

RS 232 cables (scale - Ethernet)  
 PUE 7.1 Weighing Terminal  
 RS 232, RS 485 cables  
 IN/OUT Cables

Powerbanks  
 PUE HY10 Weighing Terminal  
 Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX  
 Weighing Terminal  
 RS 232 – USB Converter

## Software (Additional Fee)

- MWMH Manager [WX-010-0103]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]

## Device dimensions



PL.16 - 32.HRP.H

PL.62-2000.HRP.H

Scale type	A1	A2	H
PL.(16-32).HRP.H	360	280	180±5
PL.(62-150).HRP.H	500	400	180±5
PL.150.2.HRP.H	500	500	180±5
PL.(150.1-300).HRP.H	800	600	180±5
PL.(300.1-1100).HRP.H	1000	800	180±5
PL.(2000).HRP.H	1250	1000	180±5

Dimensions in mm