



More information on the website
radwag.com/en/info,w1,140

PUE CY10 Weighing Terminal

WX-008-0217



The drawings, photos and graphics used are for illustrative purposes only.

Functions

- | | | | |
|---|---|---|---|
|  Autotest |  Dosing |  Percent Weighing |  Parts counting |
|  Peak hold |  Formulation |  Newton unit measurement |  Statistics |
|  Checkweighing |  IR sensors |  GLP Procedures |  Animal weighing |
|  Pipettes Calibration |  Air density correction |  Density determination |  Differential weighing |
|  Ambient conditions monitoring |  Statistical Quality Control |  Packaged Goods Control |  ALIBI Memory |
|  Wi-Fi | | | |

Datasheet

Physical parameters

Display 10" graphic colour touchscreen

| Construction | |
|--|---|
| Protection class | IP 43 |
| Housing | ABS + aluminum |
| Communication interface | |
| Communication interface | 2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot |
| Electrical parameters | |
| Power supply | 12 – 15 V DC |
| Power consumption | 1 A |
| Metrological parameters | |
| Maximum quantity of verification units | 10000 |
| Minimum voltage per verification unit | 0.4 μ V |
| Maximum voltage per verification unit | 3.25 μ V |
| Minimum load cell impedance | 50 Ω |
| Maximum load cell impedance | 1200 Ω |
| Load cell excitation voltage | 5V |
| Maximum increase of signal | 19.5 mV |
| Connection of load cells | 4 or 6 wires + ekran |
| Environmental conditions | |
| Operating temperature | -10 – +40 °C |
| Components and software | |
| Operating system | Linux |
| Processor | quad-core Broadcom 1.5 GHz |
| Memory | 16 GB, 2GB RAM |
| Multiple range | YES |
| Features of use | |
| Max number of platforms | max.2 |

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Compatible with (Additional Fee)

MediaBox
Mild steel powder coated weighing platforms
RFID Tags
Power Adapters
Additional Weighing platforms Module
Additional modules
Platforms in plastic casing

Protective cover for balances
Barcode scanners
RS 232, RS 485 cables
Label Printers
Fingerprint Reader
RS 232 – USB Converter
Receipt Printer

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions W x D x H

