



More information on the website  
[radwag.com/us/info,w1,1BV](https://radwag.com/us/info,w1,1BV)

# MAS 82/220 Weighing Module



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Maximum capacity [Max]	82 / 220 g
Minimum load	1 mg
Preload range	8,2 g
Readability [d]	0,01 / 0,1 mg
Tare range	-220 g
Standard minimum weight (USP)	40 mg
Standard minimum weight (U=1%, k=2)	4 mg
Repeatability (Max)	0,1 mg
Repeatability (5% Max)	0,02 mg
Linearity	±0,06 / 0,2 mg
Stabilization time	6 / 2 s
Adjustment	internal (automatic)
<b>Construction</b>	
Protection class	IP 32
Housing	aluminum

Communication interface	RS232, USB-B
Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%
<b>Physical parameters</b>	
Weighing pan dimensions	ø42 mm
Device dimensions	175x236x105 mm
Packaging dimensions	515×340×295 mm
Net weight	3 kg



## Accessories

Antivibration tables  
Professional Weighing Tables  
RS 232, RS 485 cables

RS 232 – USB Converter  
RS 232 cables (scale - printer)

## Software

- RAD Key [WX-010-0005]
- RADWAG Development Studio [WX-010-0104]

- R Panel [WX-010-0187]

## Device dimensions

