



More information on the website
radwag.com/en/info,w1,1Q7

DWR 1500 H1 Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 g
Readability [d]	0.5 g
Tare range	-1500 g
Physical parameters	
Display	12" graphic colour touchscreen
Operating pressure	6 - 8 bar
Construction	
Protection class	IP 55, IP 65
Environmental conditions	
Operating temperature	0 ÷ +40 °C
Air consumption	1 liter/measurement
Features of use	
Capacity	max 80 pcs/min



Extra payment for verification

Accessories

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

Barcode scanners

Label Printers

RS 232, RS 485 cables

Keypad, external switches

USB adapter

Receipt Printer

USB cable (scale - printer)

Software

• Label Editor R02 [WX-010-0094]