



More information on the website
radwag.com/ja/info,w1,36D

UYA 6.5Y

WL-109-0002



The drawings, photos and graphics used are for illustrative purposes only.



Autotest



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit measurement



Statistics



Checkweighing



IR sensors



GLP Procedures



Animal weighing



Pipettes Calibration



Air density correction



Density determination



Differential weighing



Ambient conditions monitoring



Statistical Quality Control



Packaged Goods Control



ALIBI Memory



Wi-Fi



Specifications

Capacity [Max]

6,1 g

Resolution

0,01 mg

Wzrost	
Wzrost [d]	0,1 µg
Wzrost [e]	1 mg
Wzrost	-6,1 g
Wzrost [5% Max]	0,2 µg
Wzrost [Max]	0,45 µg
Wzrost (USP)	0,4 mg
Wzrost (U=1%, k=2)	0,04 mg
Wzrost [5% Max]	0,4 µg
Wzrost [Max]	0,8 µg
Wzrost	±1,5 µg
Wzrost	1,5 µg
Wzrost	$1 \times 10^{-6} 700 \text{ mA} \times \text{Rt} - 1 \text{ A} \times \text{Rt}$
Wzrost	10 - 20 s
Wzrost	Wzrost (Wzrost)
OIML	I
Wzrost	
Wzrost	20
Wzrost	10" Wzrost + Wzrost Wzrost
Wzrost
Wzrost	ø 90×90 mm
Wzrost	ø16 mm
Wzrost	560×350×252 mm
Wzrost	750×492×595 mm
Wzrost	9,1 kg
Wzrost	16,5 kg
Wzrost	
Wzrost	IP 43
Wzrost	
Wzrost	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Wzrost	
Wzrost	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A : 12 – 15V DC 1,4A max*
Wzrost	
Wzrost	+10 – +40 °C
Wzrost	±0,3 °C / 1 h (±1 °C / 8 h)
Wzrost	40% – 80%
Wzrost	±1% / h (±4% / 8 h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

☐☐☐☐☐ (Additional Fee)

☐☐☐☐☐☐☐

RFID☐☐

☐☐☐

☐☐☐☐☐☐

☐☐☐☐☐☐

☐☐☐☐☐☐☐☐☐☐

☐☐☐☐☐☐☐☐☐☐☐☐☐☐☐☐

☐☐☐☐☐☐☐☐

☐☐☐☐☐☐☐☐

RS 232☐RS 485 ☐☐☐☐

☐☐☐☐☐☐☐

☐☐☐☐☐☐☐☐☐☐☐☐☐☐☐☐

THBR 2.0 ☐☐☐☐ - ☐☐☐☐ - ☐☐☐☐☐☐☐☐☐☐

RS 232☐RS 485 ☐☐☐☐

☐☐☐

☐☐☐☐☐☐☐☐

☐☐☐☐☐☐

☐☐☐☐☐☐☐☐

☐☐☐☐☐☐ (Additional Fee)

- [WX-010-0099]
- [WX-010-0005]
- [WX-010-0107]
- [WX-010-0173]

- [WX-010-0038]
- [WX-010-0094]
- [WX-010-0080]
- [WX-010-0104]

☐☐☐☐☐☐☐☐

