



More information on the website  
[radwag.com/us/info,w1,3MS](http://radwag.com/us/info,w1,3MS)

# HX5.EX-1.4.60.H6/Z 4 Load Cell Platform Scale, pit version



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

## Datasheet

|                            |                   |
|----------------------------|-------------------|
| Maximum capacity [Max]     | 60 kg             |
| Minimum load               | 400 g             |
| Readability [d]            | 20 g              |
| Tare range                 | -60 kg            |
| <b>Physical parameters</b> |                   |
| Display                    | 5" graphic colour |
| Cable length               | 3 m               |

| Physical parameters     |   |
|-------------------------|---|
| Weighing pan dimensions | 800×800 mm                              |
| Packaging dimensions    | 1000×1000×530 mm                        |
| Net weight              | 62,8 kg                                 |
| Gross weight            | 63 kg                                   |
| Construction            |   |
| Protection class        | IP 67 construction, IP 66 / 68 terminal |
| Construction            | Stainless steel AISI304                 |
| ATEX Certification      | II 2G Ex ib IIB T4 Gb                   |
| IECEX Certification     | Ex ib IIB T4 Gb                         |
| Indicator               | PUE HX5.EX-1                            |
| Communication interface | 2×RS232, RS485                          |
| Power supply            | 100 – 240 V AC 50/60 Hz                 |
| Power consumption max.  | 15 W                                    |
| Operating temperature   | -10 – +40 °C                            |
| Relative humidity       | 10% – 85% RH no condensation            |



Extra payment for verification



## Accessories

Communication modules  
Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX  
Weighing Terminal

Receipt Printer

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]