



More information on the website
radwag.com/us/info,w1,3S1

MA 110.5Y.IC Moisture Analyzer



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Statistics
-  IR sensors
-  GLP Procedures
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Drying modes
-  Samples drying
-  Moisture content analysis
-  Dry mass determination
-  Wi-Fi

Datasheet

Maximum capacity [Max]	110 g
Readability [d]	1 mg
Verification unit [e]	10 mg
Tare range	-110 g
Adjustment	internal (automatic)
OIML Class	II
Maximum sample weight	110 g
Heating module	IR emitter

Moisture content repeatability	+/-0,05% (sample ~ 2g), +/-0,01% (sample ~ 10g)
Moisture content readability	0,001%
Drying temperature range	Max 160 °C
Physical parameters	
Leveling system	semi-automatic - LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber	automatic
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions	540×610×470 mm
Net weight	5,3 kg
Gross weight	6,8 kg
Construction	
Protection class	IP 43
Features of use	
Display mode	%MC, %DC, %ATRO MC, %ATRO DC, g, g/kg MC, g/kg DC, -%MC
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	
Power supply	100V – 120V AC 50/60Hz or 200V-240V AC 50/60Hz
Power consumption	6 W
Heating module power	450 W
Operating temperature	
Operating temperature	+10 ÷ +40 °C
Mass indication control	
Mass indication control	External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer)
Mass indication control	External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer)
Internal adjustment	For .IC models only, GLP report
External adjustment	For all models, GLP report
Drying temperature control	One- or two-point, depending on the drying profile (equipment: GT105k-12/Z Control Thermometer)
Moisture content indication control	Certified MV Test Set
Internal / External adjustment	
Internal / External adjustment	Depending on the type of moisture analyzer, GLP report
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (equipment: GT105k-12/Z Control Thermometer)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

Antivibration tables
Moisture analyzer accessories
Additional modules
Barcode scanners
Receipt Printer

Fingerprint Reader
Protective cover for balances
RS 232, RS 485 cables
RS 232 cables (scale - printer)
RS 232 – RS 485 Converter

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

