



More information on the website  
[radwag.com/en/info,w1,3SB](https://radwag.com/en/info,w1,3SB)

# DWT/HL 1500/HPC Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Metrological parameters  |                                   |
|--------------------------|-----------------------------------|
| Maximum capacity [Max]   | 1500 g                            |
| Minimum load             | 20 g                              |
| Readability [d]          | 1 g                               |
| Tare range               | -1500 g                           |
| Physical parameters      |                                   |
| Display                  | 5.7" resistive colour touchscreen |
| Construction             |                                   |
| Protection class         | IP 55                             |
| Environmental conditions |                                   |
| Operating temperature    | 0 ÷ +40 °C                        |
| Features of use          |                                   |
| Capacity                 | max 60 pcs/min                    |
| Speed                    | 0.1-1 m/s                         |



Extra payment for verification

## Accessories

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

Barcode scanners

Label Printers

RS 232, RS 485 cables

Keypad, external switches

USB adapter

Receipt Printer

USB cable (scale - printer)

## Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]