



More information on the website
radwag.com/us/info,w1,452























XA 21/52.5Y.M.A Microbalance

WL-109-1004



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Automatic sliding door
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	21 / 52 g
Minimum load	0,1 mg
Readability [d]	1 / 5 µg

Verification unit [e]	1 mg
Tare range	-52 g
Standard repeatability [5% Max]	1,5 µg
Standard repeatability [Max]	6 µg
Standard minimum weight (USP)	3 mg
Standard minimum weight (U=1%, k=2)	0,3 mg
Permissible repeatability [5% Max]	2,4 µg
Permissible repeatability [Max]	8 µg
Linearity	±20 µg
Eccentric load deviation	20 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	~ 3,5 s
Adjustment	internal (automatic)
OIML Class	I

Physical parameters

Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, weighing pan, weighing pan shield, power supply, brush, fabric dust cover.
Weighing chamber dimensions	199×170×217 mm
Weighing pan dimensions	ø30 mm
Packaging dimensions	750×492×595 mm
Net weight	14,5 kg
Gross weight	18,9 kg

Construction

Protection class	IP 43
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

MediaBox

RFID Tags

Antivibration tables

Power Adapters

Protective cover for balances

RS 232, RS 485 cables

Additional modules

Anti-Draft Chamber for Microbalances

Professional Weighing Tables

Protective cover for balances

Barcode scanners

Automatic feeders

MICRO-KIT - Set of Holders for Microscale Glassware

Label Printers

THBR 2.0 System - Ambient Conditions Monitoring

RS 232, RS 485 cables

Adapters for pipettes calibration

Anti-Draft Chamber for XA 4Y and XA 5Y Balances

Weighing dishes

Antistatic ionizer

Receipt Printer

Fingerprint Reader

RS 232 – USB Converter

Under-pan weighing

Software (Additional Fee)

• E2R Weighing [WX-010-0099]

• RAD Key [WX-010-0005]

• RADWAG Remote Desktop [WX-010-0107]

• RADWAG Development Studio [WX-010-0104]

• E2R Weighing Records [WX-010-0038]

• Label Editor R02 [WX-010-0094]

• Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

