



More information on the website
radwag.com/en/info,w1,4JG

AKM-2.50.1.5Y Automatic Mass Comparators

WL-411-0015



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
E0 Calibration Range	5 – 50 * kg
E1 Calibration Range	5 – 50 kg
E2 Calibration Range	5 – 50 kg
F1 Calibration Range	5 – 50 kg
F2 Calibration Range	5 – 50 kg
M1 Calibration Range	-
M2 Calibration Range	-
Maximum capacity [Max]	50.5 kg
Readability [d]	0.1 mg
Standard repeatability [5% Max]	0.4 mg
Standard repeatability [Max]	0.6 mg
Permissible repeatability	1 mg
Eccentricity (tested load)	0 mg
Electric compensation range	-500 – +500 g

Metrological parameters	
Stabilization time	30 s
Adjustment	internal (automatic)
Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	∅100 mm - self centering
Weighing device dimensions	1770×800×1280 mm
Controlling device dimensions	249×170×72 mm
Packaging dimensions	1770×900×1100 mm
Net weight	260 kg
Net weight	260 kg
Gross weight	380 kg
Gross weight	380 kg
Supplementary weights internal	-
Supplementary weights external	-
Communication interface	
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	+15 – +30 °C
Operating temperature change rate	±0.5 °C / 12 h (±0.3 °C / 4 h)
Relative humidity	40% – 60%
Relative humidity change rate	±5% / 12 h (3% / 4 h)

Repeatability is expressed as a standard deviation determined for 6 ABBA cycles. Standard deviation is experimentally determined under ambient conditions for calibration of E1 class mass standards specified in OIML R111 (Table C.1.) document.

E0 standard determined from 1∕5 limiting error according to OIML R111 for class E1

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

RFID Tags
 Additional modules
 Protective cover for balances
 Barcode scanners
 RS 232, RS 485 cables


THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 RS 232, RS 485 cables
 RS 232 cables (scale - printer)

Software (Additional Fee)

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]

- RMCS Lite [WX-010-0164]

Device dimensions



AKM-2