



More information on the website
radwag.com/us/info,w1,4JG

AKM-2.50.1.5Y Automatic Mass Comparators



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

E1 Calibration Range	5 – 50 kg
E2 Calibration Range	5 – 50 kg
F1 Calibration Range	5 – 50 kg
F2 Calibration Range	5 – 50 kg
M1 Calibration Range	-
M2 Calibration Range	-
Maximum capacity [Max]	50,2 kg
Readability [d]	0,1 mg
Standard repeatability [5% Max]	0,4 mg
Standard repeatability [Max]	0,6 mg
Permissible repeatability	1 mg
Eccentricity (tested load)	0 mg
Electric compensation range	0 g – 50,5 kg
Stabilization time	30 s
Adjustment	external

Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	ø100 mm - self centering
Weighing device dimensions	1770×800×1280 mm
Controlling device dimensions	249×170×72 mm
Packaging dimensions	1770×900×1100 mm
Net weight	260 kg
Net weight	260 kg
Gross weight	380 kg
Gross weight	380 kg
Supplementary weights internal	-
Supplementary weights external	-
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+15 – +30 °C
Operating temperature change rate	±0,5 °C / 12 h (±0,3 °C / 4 h)
Relative humidity	40% – 60%
Relative humidity change rate	±5% / 12 h (3% / 4 h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

RFID Tags
 Additional modules
 Protective cover for balances
 Barcode scanners
 RS 232, RS 485 cables



THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 RS 232, RS 485 cables
 RS 232 cables (scale - printer)

Software

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]

- RMCS Lite [WX-010-0164]

Device dimensions



AKM-2