



More information on the website  
[radwag.com/us/info,w1,4JG](http://radwag.com/us/info,w1,4JG)

# AKM-2.50.1.5Y Automatic Mass Comparators



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

E1	5 kg ÷ 50 kg
E2	5 kg ÷ 50 kg
F1	5 kg ÷ 50 kg
F2	5 kg ÷ 50 kg
M1	-
M2	-
Maximum capacity [Max]	50,2 kg
Readability [d]	0,1 mg
Standard repeatability [5% Max]	0,4 mg
Standard repeatability [Max]	0,6 mg
Permissible repeatability	1 mg
Eccentricity (tested load)	0 mg
Electric compensation range	0 g ÷ 50,5 kg
Stabilization time	30 s
Adjustment	external

Physical parameters	
Display	10" graphic colour touchscreen
Weighing pan dimensions	ø100 mm
Weighing device dimensions	1770×800×1280 mm
Controlling device dimensions	249×170×72 mm
Packaging dimensions	1770×900×1100 mm
Net weight	260 kg
Net weight	260 kg
Gross weight	380 kg
Gross weight	380 kg
Supplementary weights internal	-
Supplementary weights external	-
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+15 ÷ +30 °C
Operating temperature change rate	±0,5°C/12h (±0,3°C/4h)
Relative humidity	40% ÷ 60%
Relative humidity change rate	±5%/12h (3%/4h)

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

RFID Tags  
 Additional modules  
 Protective cover for balances  
 Barcode scanners  
 RS 232, RS 485 cables



THBR 2.0 System - Ambient Conditions Monitoring  
 Receipt Printer  
 Fingerprint Reader  
 RS 232, RS 485 cables  
 RS 232 cables (scale - printer)

## Software

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]

- RMCS Lite [WX-010-0164]

## Device dimensions



AKM-2