



More information on the website
radwag.com/en/info,w1,4P9

PD9330-AR Barcode Scanner



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Construction	
Protection class	IP 65
Communication interface	
Communication interface	RS232, USB
Environmental conditions	
Operating temperature	-20 ÷ +50 °C
Storage temperature	-40 ÷ +70 °C
Physical parameters	
Device dimensions	212×110×74 mm
Drop resistance [m]:	2
Operated barcodes:	1D, GS1 Databar
Readout technology:	Single line laser
Required code contrast [%]:	25

Permissible ambient humidity [%]:

0% ÷ 95%

Compatible with

MA X7.IC.A Moisture Analyzer	WPY Scales for PGC
MUYA Modules	XA 5Y.A Analytical Balance
HX7 H Stainless steel Multifunctional Scale	HX7.4 H Multifunctional Stainless Steel Platform Scale
HX7.4N H Multifunctional Stainless Steel Ramp Scale	HX7.4P2 Multifunctional Beam Scales
HX7.4C Multifunctional Platform Scale	WAY 5Y.KO Manual Mass Comparator
HX7 HR Multifunctional Scale	UYA 5Y Ultra-Microbalance
XA 5Y.M.A.P Microbalance	MA 5Y.IC Moisture Analyzer
WPY Multifunctional Scale	MA R Moisture Analyzer
Microbalance for Pipette Calibration MYA 5Y.P	AS 5Y Analytical Balance
HY10.HRP.H Stainless steel High Resolution Scale	AK-4 Automatic Mass Comparator
MA 5Y Moisture Analyzer	AKM-2 Automatic Mass Comparator
5Y.PM Precision Balance	PS R2.H Precision Balance
Microbalance for Filters MYA 5Y.F	HY10.H Scales for PGC
HX7.4P2 H Multifunctional Stainless Steel Beam Scales	CY10 Precision Balance
TMX H Stainless steel Multifunctional Scale	XA 5Y.F Analytical Balance for Filters
WLY Scales for PGC	WLY Precision Balance
MA X2.IC.A Moisture Analyzer	UMA Automatic Mass Comparator
AS X7 Analytical Balance	APP 5Y.KO Manual Mass Comparator
PS X2 Precision Balance	Robotic Mass Comparators
AS X2 PLUS Analytical Balance	Density Measurement
TMX Multifunctional Scale	MYA 5Y Microbalance
XA 5Y.M.A Microbalance	PS R1 Precision Balance
PS R2 Precision Balance	XA 5Y Analytical Balance
WLC X2 Precision Balance	MA X2.A Moisture Analyzers
WLC X7 Precision Balance	5Y.PM.KB Manual Mass Comparator
HX7.4N H.LD Multifunctional Stainless Steel Ramp Scale	AS R2 PLUS Analytical Balance
PS X2 Balances for PGC	PUE C32 Weighing Terminal
DWT/RC/HYF Checkweighers	PUE 7.1 Weighing Terminal
PUE CY10 Weighing Terminal	PUE HX7 Weighing Terminal
CY10 Multifunctional Scale	PUE 5 Weighing Terminal
HX7.4P H Multifunctional Stainless Steel Pallet Scales	PS 5Y Precision Balance
MA X2.A Moisture Analyzer	Automatic Vacuum Mass Comparators
HY10 Multifunctional Scale	PMV 5Y Moisture Analyzer
HY10 H Stainless Steel Multifunctional Scale	XA 5Y.KO Manual Mass Comparator
HRP 5Y.KO Mass Comparator	HRP 5Y.KB Mass Comparator
HY10.HRP High Resolution Scale	XA 5Y.M Microbalance
C32.PM Precision Balance	UYA 5Y.KO Manual Mass Comparator
PUE 7.1.HRP High Resolution Scale	AS R1 PLUS Analytical Balances
Automatic Device for Multichannel Pipette Calibration	Ultra-Microbalance for Filters UYA 5Y.F
HX7 Multifunctional Scale	HX7.4P Multifunctional pallet scales
MA X7.A Moisture Analyzer	Nano-Comparator NANO.AK-4.500.5Y
HX7.4 H/Z Multifunctional Stainless Steel Platform Scale, pit version	XA 5Y.M.A.S Microbalance
PS X7 Precision Balance	