



More information on the website
radwag.com/de/info,w1,5D0

4-Sensor Plattformwaage HX5.EX-1.4.600 C8/9



The drawings, photos and graphics used are for illustrative purposes only.

Funktionen



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Technische Daten

Messtechnische Parameter	
Wägebereich [Max]	600 kg
Min. Belastung	4 kg
Zifferschritt [d]	200 g
Tarierbereich	-600 kg
Physikalische Parameter	
Display	5" grafisch farbiger
Kabellänge	3 m

Physikalische Parameter	
Waagschale	1200×1500 mm
Nettogewicht	142,8 kg
Bruttogewicht	143 kg
Konstruktion	
Schutzart	IP 65 Konstruktion, IP 66/68 Messgerät
Konstruktion	pulverbeschichteter Stahl St3S
Zertifizierung ATEX	II 2G Ex ib IIB T4 Gb
Zertifizierung IECEx	Ex ib IIB T4 Gb
Messgerät	PUE HX5.EX-1
Kommunikationsschnittstellen	
Schnittstellen	2×RS232, RS485
Elektrische Parameter	
Stromversorgung	100 – 240 V AC 50/60 Hz
Maximaler Leistungsaufnahme	15 W
Umgebungsbedingungen	
Umgebungstemperatur	-10 – +40 °C
Relative Luftfeuchtigkeit	10% – 85% RH ohne Kondensation



Additional fee for verification



Zubehör (Additional Fee)

Kommunikationsmodul
Eigensichere Stromversorgung für EX-Waage

Thermische Drucker

Software (Additional Fee)

- E2R Wägung [WX-010-0099]
- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]

- E2R Evidenz [WX-010-0038]
- Etiketten-Editor R02 [WX-010-0094]
- RLAB [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]