



More information on the website
radwag.com/de/info,w1,5D0

4-Sensor Plattformwaage HX5.EX-1.4.600 C8/9



The drawings, photos and graphics used are for illustrative purposes only.

Funktionen



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Technische Daten

| Messtechnische Parameter | |
|--------------------------|----------------------|
| Wägebereich [Max] | 600 kg |
| Min. Belastung | 4 kg |
| Zifferschritt [d] | 200 g |
| Tarierbereich | -600 kg |
| Physikalische Parameter | |
| Display | 5" grafisch farbiger |
| Kabellänge | 3 m |

| Physikalische Parameter | |
|------------------------------|--|
| Waagschale | 1200×1500 mm |
| Nettogewicht | 142,8 kg |
| Bruttogewicht | 143 kg |
| Konstruktion | |
| Schutzart | IP 65 Konstruktion, IP 66/68 Messgerät |
| Konstruktion | pulverbeschichteter Stahl St3S |
| Zertifizierung ATEX | II 2G Ex ib IIB T4 Gb |
| Zertifizierung IECEx | Ex ib IIB T4 Gb |
| Messgerät | PUE HX5.EX-1 |
| Kommunikationsschnittstellen | |
| Schnittstellen | 2×RS232, RS485 |
| Elektrische Parameter | |
| Stromversorgung | 100 – 240 V AC 50/60 Hz |
| Maximaler Leistungsaufnahme | 15 W |
| Umgebungsbedingungen | |
| Umgebungstemperatur | -10 – +40 °C |
| Relative Luftfeuchtigkeit | 10% – 85% RH ohne Kondensation |



Additional fee for verification



Zubehör (Additional Fee)

Kommunikationsmodul
Eigensichere Stromversorgung für EX-Waage

Thermische Drucker

Software (Additional Fee)

- E2R Wägung [WX-010-0099]
- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]

- E2R Evidenz [WX-010-0038]
- Etiketten-Editor R02 [WX-010-0094]
- RLAB [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]