



More information on the website  
[radwag.com/en/info,w1,5DT](http://radwag.com/en/info,w1,5DT)

# MA 210.5Y.IC Moisture Analyzer



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Statistics
-  IR sensors
-  GLP Procedures
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Drying modes
-  Samples drying
-  Moisture content analysis
-  Dry mass determination
-  Wi-Fi

## Datasheet

| Metrological parameters |                      |
|-------------------------|----------------------|
| Maximum capacity [Max]  | 210 g                |
| Readability [d]         | 1 mg                 |
| Verification unit [e]   | 10 mg                |
| Tare range              | -210 g               |
| Adjustment              | internal (automatic) |
| OIML Class              | II                   |
| Maximum sample weight   | 210 g                |

| <b>Metrological parameters</b>      |  |
|-------------------------------------|--|
| Heating module                      | IR emitter   |
| Moisture content repeatability      | ±0.05 % (sample ~ 2 g), ±0.01 % (sample ~ 10 g)  |
| Moisture content readability        | 0.001 %  |
| Drying temperature range            | Max 160 °C   |
| <b>Physical parameters</b>          |  |
| Leveling system                     | semi-automatic – LevelSENSING  |
| Display                             | 10" graphic colour touchscreen   |
| Weighing chamber                    | automatic  |
| Maximum sample height               | 20 mm  |
| Weighing pan dimensions             | ø90, h= 8 mm   |
| Packaging dimensions                | 540×610×470 mm   |
| Net weight                          | 5.4 kg   |
| Gross weight                        | 6.9 kg   |
| <b>Construction</b>                 |  |
| Protection class                    | IP 43  |
| <b>Features of use</b>              |  |
| Display mode                        | %MC, %DC, %ATRO MC, %ATRO DC, g, g/kg MC, g/kg DC, -%MC  |
| Drying method                       | 4 drying profiles (standard, fast, step, mild)   |
| Finish mode                         | 4 modes (automatic, manual, time-defined, user-defined)  |
| Additional functions                | sample traceability  |
| <b>Communication interface</b>      |  |
| Communication interface             | 2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot   |
| <b>Electrical parameters</b>        |  |
| Power supply                        | 100 – 120 V AC 50/60 Hz or 200-240 V AC 50/60 Hz   |
| Power consumption                   | 6 W  |
| Heating module power                | 450 W  |
| <b>Environmental conditions</b>     |  |
| Operating temperature               | +10 – +40 °C   |
| <b>SOP – metrological tests</b>     |  |
| Mass indication control             | External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer)                           |
| Mass indication control             | External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer)                           |
| Drying temperature control          | One- or two-point, depending on the drying profile (equipment: GT105k-12/Z Control Thermometer)                  |
| Moisture content indication control | Certified MV Test Set  |
| Drying temperature adjustment       | Three-point adjustment at defined temperatures, programmable values (equipment: GT105k-12/Z Control Thermometer) |

<sup>1</sup> Barcode scanners, available as weighing instrument accessory, communicate with the instrument via USB interface exclusively.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

Antivibration Tables  
Moisture analyzer accessories  
Additional modules  
Barcode scanners  
Receipt Printer

Fingerprint Reader  
Protective cover for balances  
RS 232, RS 485 cables  
RS 232 cables (scale - printer)  
RS 232 – RS 485 Converter

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

## Device dimensions

