



More information on the website  
[radwag.com/us/info,w1,5WG](http://radwag.com/us/info,w1,5WG)

# C315.60/150.C2.K Load Cell Platform Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

## Datasheet

|                        |           |
|------------------------|-----------|
| Maximum capacity [Max] | 60/150 kg |
| Minimum load           | 400 g     |
| Readability [d]        | 20/50 g   |
| Verification unit [e]  | 20/50 g   |
| Tare range             | -150 kg   |
| OIML Class             | III       |

| Physical parameters         |                                     |
|-----------------------------|-------------------------------------|
| Display                     | LCD (backlit)                       |
| Weighing pan dimensions     | 400×500 mm                          |
| Packaging dimensions        | 720×620×210 mm                      |
| Net weight                  | 12,5 kg                             |
| Gross weight                | 15 kg                               |
| Cable length                | 2,5 m                               |
| Indicator                   | C315                                |
| Construction                |                                     |
| Protection class            | IP 65 construction, IP 43 indicator |
| Construction                | mild steel St3S                     |
| Weighing pan material       | Stainless steel AISI304             |
| Communication interface     | RS232                               |
| Optional interfaces         | RS232                               |
| Power supply                | 100 – 240 V AC 50/60 Hz and battery |
| Power consumption max.      | 5 W                                 |
| Operation time on batteries | max 8h                              |
| Operating temperature       | -10 ÷ +40 °C                        |
| Storage temperature         | -10 ÷ +50 °C                        |
| Relative humidity           | 10% ÷ 85% RH no condensation        |



Extra payment for verification



## Accessories

Antivibration tables  
 Power Adapters  
 RS 232 cables (scale - printer)  
 Stands, wall mounting kits and mounting brackets  
 Cigarette lighter receptacle power supply cables  
 Displays  
 Displays  
 RS 232, RS 485 cables

RS 232 – Ethernet Converter  
 AP2-1 Current Loop Unit  
 RS 232, RS 485 cables  
 RS 232 – USB Converter  
 RS 232 cables (scale - printer)  
 RS 232 – RS 485 Converter  
 Receipt Printer

## Software

- RAD Key [WX-010-0005]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- R Panel [WX-010-0187]

## Device dimensions



C315.F1.M

C315.F1.R



C315.C2.M

C315.C2.K

