



More information on the website
radwag.com/us/info,w1,71J

CY10.3.D2.K.M3 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

Datasheet

Maximum capacity [Max]	3 kg
Minimum load	20 g
Readability [d]	1 g
Verification unit [e]	1 g
Tare range	-3 kg
Max readability for non-verified scale	0,1 g
Stabilization time	2 s
Adjustment	external

OIML Class	III
Physical parameters	
Leveling system	manual
Display	10" graphic colour touchscreen
Weighing pan dimensions	195×195 mm
Packaging dimensions	530×310×150 mm
Net weight	3,7 kg
Gross weight	4,6 kg
Cable length	1 m
Multiple range	YES
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	
Power supply	12÷15V DC
Power consumption	1A
Operating temperature	
Operating temperature	-10 ÷ +40 °C
Storage temperature	-25 ÷ +70 °C
Features of use	
Max number of platforms	max.2

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox

Mild steel powder coated weighing platforms
 RFID Tags
 Power Adapters
 Additional Weighing platforms Module
 Mild steel powder coated weighing platforms
 Additional modules
 Platforms in plastic casing

Protective cover for balances

Barcode scanners
 Label Printers
 RS 232, RS 485 cables
 Fingerprint Reader
 RS 232 – USB Converter
 Receipt Printer

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

