



More information on the website  
[radwag.com/us/info,w1,72Q](http://radwag.com/us/info,w1,72Q)

# CY10.30.F1.K.M3 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

Maximum capacity [Max]	30 kg
Minimum load	200 g
Readability [d]	10 g

Verification unit [e]	10 g
Tare range	-30 kg
Max readability for non-verified scale	1 g
Stabilization time	2 s
Adjustment	external
OIML Class	III
<b>Physical parameters</b>	
Leveling system	manualny
Display	10" graphic colour touchscreen
Weighing pan dimensions	300×300 mm
Packaging dimensions	500×390×410 mm
Net weight	6,3 kg
Gross weight	7,1 kg
Cable length	1 m
Multiple range	YES
<b>Construction</b>	
Protection class	IP 43
Housing	steel + ABS
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	12÷15V DC
Power consumption	1A
Operating temperature	-10 ÷ +40 °C
Storage temperature	-25 ÷ +70 °C
<b>Features of use</b>	
Max number of platforms	max.2

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

MediaBox  
Mild steel powder coated weighing platforms  
RFID Tags  
Power Adapters  
Additional Weighing platforms Module  
Mild steel powder coated weighing platforms  
Additional modules  
Platforms in plastic casing

Protective cover for balances  
Barcode scanners  
Label Printers  
RS 232, RS 485 cables  
Fingerprint Reader  
RS 232 – USB Converter  
Receipt Printer

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

