



# UMA 200.5Y Automatic Mass Comparator

More information on the website  
[radwag.com/us/info,w1,73P](http://radwag.com/us/info,w1,73P)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

E1 Calibration Range	1 – 200 g
E2 Calibration Range	1 – 200 g
F1 Calibration Range	1 – 200 g
F2 Calibration Range	1 – 200 g
Maximum capacity [Max]	210 g
Readability [d]	0,001 mg
Standard repeatability [5% Max]	2,5 µg
Standard repeatability [Max]	4 µg
Permissible repeatability	6 µg
Eccentricity (tested load)	0 mg
Electric compensation range	-1 g – +10 g
Stabilization time	30 s
Adjustment	external
<b>Physical parameters</b>	
Display	10" graphic colour touchscreen

Physical parameters	
Weighing pan dimensions	ø30 mm
Weighing device dimensions	700×585×720 mm
Controlling device dimensions	460×250×195 mm
Packaging dimensions	1200×1000×1566 mm
Net weight	114,3 kg
Gross weight	204,3 kg
Supplementary weights internal	automatic
Supplementary weights external	-
Magazine positions	30
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+15 – +30 °C
Operating temperature change rate	±0,5 °C / 12 h (±0,3 °C / 4 h)
Relative humidity	40% – 60%
Relative humidity change rate	±5% / 12 h (3% / 4 h)

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

RFID Tags  
 Antivibration tables  
 Additional modules  
 Protective cover for balances  
 Barcode scanners  
 RS 232, RS 485 cables




THBR 2.0 System - Ambient Conditions Monitoring  
 Receipt Printer  
 Fingerprint Reader  
 RS 232, RS 485 cables  
 RS 232 cables (scale - printer)

## Software

• RAD Key [WX-010-0005]  
 • RMCS System Network Management of Calibration Process [WX-010-0048]



• RMCS Lite [WX-010-0164]

## Device dimensions



UMA-100, UMA-1000

UMA-control unit



UMA-5