


























More information on the website
radwag.com/en/info,w1,7D8

XA 6/21.5Y.M.A Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Automatic sliding door
-  Density determination
-  Moveable range
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	6 / 21 g
Minimum load	0.1 mg

Metrological parameters	
Readability [d]	1 / 2 µg
Verification unit [e]	1 mg
Tare range	-21 g
Standard repeatability [5% Max]	1.3 µg
Standard repeatability [Max]	3.5 µg
Standard minimum weight (USP)	2.6 mg
Standard minimum weight (U=1%, k=2)	0.26 mg
Permissible repeatability [5% Max]	2 µg
Permissible repeatability [Max]	5 µg
Linearity	±9 µg
Eccentric load deviation	15 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	~ 3.5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, weighing pan, weighing pan shield, power supply, brush, fabric dust cover.
Weighing chamber dimensions	199×170×217 mm
Weighing pan dimensions	ø30 mm
Packaging dimensions	750×492×595 mm
Net weight	14.5 kg
Gross weight	18.9 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3 °C / 1 h (±1 °C / 8 h)
Relative humidity	40% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories

MediaBox
 RFID Tags
 Antivibration Tables
 Power Adapters
 Protective cover for balances
 RS 232, RS 485 cables
 Additional modules
 Anti-Draft Chamber for Microbalances
 Professional Weighing Tables
 Protective cover for balances
 Barcode scanners
 MICRO-KIT - Set of Holders for Microscale Glassware

Label Printers
 THBR 2.0 System - Ambient Conditions Monitoring
 RS 232, RS 485 cables
 Adapters for Pipettes Calibration
 Anti-Draft Chamber for XA 4Y and XA 5Y Balances
 Weighing dishes
 Antistatic ionizer
 Receipt Printer
 Fingerprint Reader
 RS 232 – USB Converter
 Under-pan weighing

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

Device dimensions

