















More information on the website  
[radwag.com/en/info,w1,7GE](http://radwag.com/en/info,w1,7GE)

# C32.30.C2.M Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Labelling
-  Plus/Minus Control
-  Percent Weighing
-  Totalizing
-  Parts counting
-  Newton unit measurement
-  Statistics
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Replaceable unit
-  ALIBI Memory

## Datasheet

Metrological parameters	
Maximum capacity [Max]	30 kg
Minimum load	200 g
Readability [d]	10 g
Tare range	-30 kg
Max readability for non-verified scale	1 g
OIML Class	III

Physical parameters	
Display	5" graphic colour
Protection class	IP 65 construction, IP 43 indicator
Weighing pan dimensions	500×400 mm
Packaging dimensions	720×620×210 mm
Net weight	12,8 kg
Gross weight	14,8 kg
Communication interface	
Communication interface	2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Power consumption max.	10 W
Optional power supply	internal rechargeable battery
Operation time on batteries	operation time up to 5 h
Environmental conditions	
Operating temperature	-10 ÷ +40 °C
Construction	
Construction	mild steel St3S
Weighing pan material	stainless steel AISI304

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

Displays  
 RS 232 cables (scale - printer)  
 Cigarette lighter receptacle power supply cables  
 Barcode scanners  
 RS 232, RS 485 cables

Label Printers  
 Keypad, external switches  
 Stands, wall mounting kits and mounting brackets  
 Receipt Printer

## Software

RAD-KEY  
 Label Editor R02  
 RADWAG Development Studio  
 R.Barcode


LabVIEW Driver  
 R-LAB  
 E2R System

## Device dimensions



C32.C2.R

C32.C2.K



C32.C2.M