



C32.25.PM Precision Balance

WL-223-0025

More information on the website
radwag.com/us/info,w1,89A



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Newton unit measurement



Statistics



IR sensors



Under-pan weighing



GLP Procedures



Animal weighing



Density determination



Replaceable unit



ALIBI Memory

Datasheet

Maximum capacity [Max]	25 kg
Minimum load	5 g
Preload range	2,5 kg
Readability [d]	0,1 g
Verification unit [e]	1 g
Tare range	-25 kg

Minimum weight (USP)	82 g
Minimum weight (U=1%,k=2)	8,2 g
Repeatability (Max)	0,1 g
Repeatability (5% Max)	0,04 g
Linearity	±0,3 g
Stabilization time	1 s
Adjustment	internal (automatic)
OIML Class	II
Physical parameters	
Leveling system	manual
Display	5" graphic colour
Weighing pan dimensions	350×260 mm
Packaging dimensions	520×520×280 mm
Net weight	11 kg
Gross weight	15,5 kg
Construction	
Protection class	IP 43
Communication interface	2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Balance: 10 – 12V DC 1A max
Operating temperature	+10 – +40 °C

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

Displays
Antivibration tables
Power Adapters
RS 232 cables (scale - printer)
Cigarette lighter receptacle power supply cables
Professional Weighing Tables
Barcode scanners
Under-pan weighing

RS 232, RS 485 cables
Displays
Displays
Stands, wall mounting kits and mounting brackets
Receipt Printer
RS 232, RS 485 cables
RS 232 cables (scale - printer)

Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- Alibi Reader PC Software [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

