



More information on the website
radwag.com/us/info,w1,89D

MYA 5.5Y Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	5,1 g
Minimum load	0,1 mg
Readability [d]	1 µg

Verification unit [e]	1 mg
Tare range	-5,1 g
Standard repeatability [5% Max]	0,6 µg
Standard repeatability [Max]	1,6 µg
Standard minimum weight (USP)	1,2 mg
Standard minimum weight (U=1%, k=2)	0,12 mg
Permissible repeatability [5% Max]	1,2 µg
Permissible repeatability [Max]	2,4 µg
Linearity	±3 µg
Eccentric load deviation	5 µg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times \text{Rt}$
Stabilization time	3,5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatyczny - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø90×90 mm
Weighing pan dimensions	ø26 mm
Packaging dimensions	750×492×595 mm
Net weight	9,1 kg
Gross weight	16 kg
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

RFID Tags
Antivibration tables
Power Adapters

RS 232, RS 485 cables
THBR 2.0 System - Ambient Conditions Monitoring
Chamber for filter weighing

Additional modules
Professional Weighing Tables
Antistatic ionizer
Protective cover for balances
Barcode scanners

Weighing dishes
Receipt Printer
Protective cover for balances
RS 232 – USB Converter
RS 232, RS 485 cables

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

