
























More information on the website
radwag.com/en/info,w1,8A1

5Y.120.PM Precision Balance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	120 kg
Minimum load	-

Metrological parameters	
Readability [d]	0.2 g
Verification unit [e]	-
Tare range	-120 kg
Minimum weight (USP)	164 g
Minimum weight (U=1%,k=2)	16.4 g
Repeatability (Max)	0.2 g
Repeatability (5% Max)	0.082 g
Linearity	±0.6 g
Stabilization time	1 s
Adjustment	internal (automatic)
OIML Class	-
Physical parameters	
Leveling system	półautomatyczny - LevelSENSING
Display	10" graphic colour touchscreen
Weighing pan dimensions	400×500 mm
Packaging dimensions	710×610×240 mm
Net weight	22 kg
Gross weight	24.5 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 16V DC 1.4A max*
Environmental conditions	
Operating temperature	+10 – +40 °C

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

MediaBox
RFID Tags
Antivibration Tables
Power Adapters
Additional modules
Professional Weighing Tables
Protective cover for balances
Barcode scanners

Under-pan weighing
RS 232, RS 485 cables
RS 232, RS 485 cables
Stands, wall mounting kits and mounting brackets
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter

Software

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]
- E2R Weighing Records [WX-010-0038]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions

