



More information on the website  
radwag.com/us/info,w1,8A1

# 5Y.120.PM Precision balance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

Maximum capacity [Max]	120 kg
Minimum load	-
Readability [d]	0,2 g

Verification unit [e]	-
Tare range	-120 kg
Minimum weight (USP)	164 g
Minimum weight (U=1%,k=2)	16,4 g
Repeatability (Max)	0,2 g
Repeatability (5% Max)	0,082 g
Linearity	±0,6 g
Stabilization time	1 s
Adjustment	internal (automatic)
OIML Class	-
<b>Physical parameters</b>	
Leveling system	półautomatyczny - LevelSENSING
Display	10" graphic colour touchscreen
Weighing pan dimensions	400×500 mm
Packaging dimensions	710×610×240 mm
Net weight	22 kg
Gross weight	24,5 kg
<b>Construction</b>	
Protection class	IP 43
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 16V DC 1,4A max*
Operating temperature	+10 – +40 °C

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

MediaBox  
RFID Tags  
Antivibration tables  
Power Adapters  
Additional modules  
Professional Weighing Tables  
Protective cover for balances  
Barcode scanners

Under-pan weighing  
RS 232, RS 485 cables  
RS 232, RS 485 cables  
Stands, wall mounting kits and mounting brackets  
Receipt Printer  
Fingerprint Reader  
RS 232 – USB Converter

## Software

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- RADWAG Remote Desktop [WX-010-0107]

## Device dimensions

