
























More information on the website
radwag.com/en/info,w1,8GY

CY10.1,5/3.D2.K.M3 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	1.5/3 kg
Minimum load	10 g

Metrological parameters	
Readability [d]	0.5/1 g
Verification unit [e]	0.5 g
Tare range	-3 kg
Stabilization time	2 s
Adjustment	external
OIML Class	III
Physical parameters	
Leveling system	manualny
Display	10" graphic colour touchscreen
Weighing pan dimensions	195×195 mm
Packaging dimensions	500×310×150 mm
Net weight	3.7 kg
Gross weight	4.6 kg
Cable length	1 m
Multiple range	YES
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	12÷15V DC
Power consumption	1A
Environmental conditions	
Operating temperature	-10 ÷ +40 °C
Storage temperature	-25 ÷ +70 °C
Features of use	
Max number of platforms	max.2

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox

Mild steel powder coated weighing platforms

RFID Tags

Power Adapters

Additional Weighing platforms Module

Mild steel powder coated weighing platforms

Additional modules

Protective cover for balances

Barcode scanners

Label Printers

RS 232, RS 485 cables

Fingerprint Reader

RS 232 – USB Converter

Receipt Printer

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions

