



More information on the website
radwag.com/en/info,w1,8PQ

XA 53.5Y.M.A.P Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Percent Weighing
-  Peak hold
-  Statistics
-  IR sensors
-  GLP Procedures
-  Pipettes Calibration
-  Air density correction
-  Automatic sliding door
-  Moveable range
-  Differential weighing
-  Ambient conditions monitoring
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters	
Maximum capacity [Max]	53 g
Minimum load	0.1 mg
Readability [d]	1 µg
Verification unit [e]	1 mg
Tare range	-53 g
Standard repeatability [5% Max]	1.5 µg

Metrological parameters	
Standard repeatability [Max]	6 µg
Standard minimum weight (USP)	3 mg
Standard minimum weight (U=1%, k=2)	0.3 mg
Permissible repeatability [5% Max]	2.4 µg
Permissible repeatability [Max]	8 µg
Linearity	±20 µg
Eccentric load deviation	20 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	~3.5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, weighing pan, weighing pan shield, power supply, automatic pipette calibration adapter: (base, bottom ring, glass vessel, pipette calibration adapter, evaporation ring, weighing pan, glass lid, mechanical closing cover, protecting screw), brush, fabric dust cover.
Weighing chamber dimensions	199×170×217 mm
Capacity	11 ml
Weighing pan dimensions	ø26 mm
Packaging dimensions	750×492×595 mm
Net weight	14.5 kg
Gross weight	18.9 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration Tables
Power Adapters
Protective cover for balances
Additional modules
Anti-Draft Chamber for Microbalances
Automatic Variable-Volume Pipettes
Professional Weighing Tables
Protective cover for balances
Barcode scanners

Workstation for Pipettes Calibration
RS 232, RS 485 cables
Label Printers
THBR 2.0 System - Ambient Conditions Monitoring
RS 232, RS 485 cables
Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Antistatic ionizer
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Under-pan weighing

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- R-Pipettes [WX-010-0026]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]