




More information on the website  
radwag.com/en/info,w1,8PT

















# WPY 0.6/1.5.D2.PGC Scale

WK-308-1046



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Dosing
-  Labelling
-  Plus/Minus Control
-  Percent Weighing
-  Totalizing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Animal weighing
-  Differential weighing
-  Packaged Goods Control
-  ALIBI Memory

## Datasheet

Metrological parameters	
Maximum capacity [Max]	0.6 / 1.5 kg
Minimum load	4 / 10 g
Readability [d]	0.2 / 0.5 g
Tare range	-1.5 kg
OIML Class	III

Physical parameters	
Display	5.7" resistive colour touchscreen
Cable length	1 m
Weighing pan dimensions	195×195 mm
Packaging dimensions	530×310×150 mm
Communication interface	
Communication interface	2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	-10 – +40 °C
Relative humidity	10% – 85% RH no condensation

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

Transponder card readers

Power Adapters

RS 232 cables (scale - printer)

Cigarette lighter receptacle power supply cables

Barcode scanners

RS 232, RS 485 cables

Label Printers

Displays

IN/OUT Cables

Keypad, external switches

Stands, wall mounting kits and mounting brackets

Receipt Printer

F1 Mass Standard - knob weights without adjustment chamber, set

AP2-1 Current Loop Unit

RS 232, RS 485 cables

Additional Weighing platforms Module

RS 232 – USB Converter

RS 232 cables (scale - printer)

## Software (Additional Fee)

• E2R Weighing [WX-010-0099]

• E2R Weighing Records [WX-010-0038]

• Audit Trail Reader [WX-010-0186]

• RADWAG Remote Desktop [WX-010-0107]

• Scale Editor 2.1 [WX-010-0173]

• E2R PGC [WX-010-0051]

• RAD Key [WX-010-0005]

• Label Editor R02 [WX-010-0094]

• R-Lab [WX-010-0080]

• RADWAG Development Studio [WX-010-0104]