




More information on the website
radwag.com/ja/info,w1,8PT

WPY 0.6/1.5.D2.PGC はかり

WK-308-1046



The drawings, photos and graphics used are for illustrative purposes only.

機能

- | | | | |
|---|---|--|--|
|  Dosing |  Labelling |  Plus/Minus Control |  Percent Weighing |
|  Totalizing |  Parts counting |  Peak hold |  Formulation |
|  Newton unit measurement |  Statistics |  Checkweighing |  IR sensors |
|  Animal weighing |  Differential weighing |  Packaged Goods Control |  ALIBI Memory |

データシート

計測パラメータ	
最大ひょう量 [Max]	0,6 / 1,5 kg
最小荷重	4 / 10 g
最小表示 [d]	0,2 / 0,5 g
風袋範囲	-1,5 kg
OIMLクラス	III

物理的パラメータ	
ディスプレイ	ホルダー
ケーブル長	1 m
計量皿寸法	195×195 mm
梱包寸法 幅×奥行×高さ	530×310×150 mm
工事中	
保護クラス	IP 43
通信インターフェース	
通信インターフェース	2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (OUT), Wi-Fi
電氣的パラメータ	
電源	100 – 240 V AC 50/60 Hz
環境条件	
動作温度	-10 – +40 °C
相対湿度	10% – 85% RH 最大距離

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



アクセサリ (Additional Fee)

トランスポンダー式カードリーダー
電源アダプタ
RS 232 ケーブル (はかり - プリンタ)
シガーライターソケット電源ケーブル
バーコードスキャナ
RS 232、RS 485 ケーブル
ラベルプリンタ
ディスプレイ
IN/OUT ケーブル

キーパッド、外部スイッチ
スタンド、壁取り付けキット、取り付けブラケット
レシートプリンタ
F1 級分銅 - 調整室なしノブ型分銅、セット
AP2-1 電流ループユニット
RS 232、RS 485 ケーブル
追加計量プラットフォームモジュール
RS 232 - USB コンバータ
RS 232 ケーブル (はかり - プリンタ)

ソフトウェア (Additional Fee)

- E2R Weighing (計量) [WX-010-0099]
- E2R Weighing Records (計量記録) [WX-010-0038]
- Audit Trail Reader (監査証跡) [WX-010-0186]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

- E2R PGC (生産管理) [WX-010-0051]
- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]