



# MA 200/1.X7.IC.A.WH Moisture Analyzer

WL-308-0037

More information on the website  
[radwag.com/en/info/w1,975](http://radwag.com/en/info/w1,975)



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

 Autotest	 Statistics	 IR sensors	 GLP Procedures
 Replaceable unit	 Statistical Quality Control	 ALIBI Memory	 Drying modes
 Samples drying	 Moisture content analysis	 Dry mass determination	 Wi-Fi

## Datasheet

Metrological parameters	
Maximum capacity [Max]	200 g
Readability [d]	0.1 mg
Tare range	-200 g
Adjustment	internal (automatic)
Maximum sample weight	200 g
Heating module	halogen
Moisture content repeatability	±0.05 % (sample ~ 2 g), ±0.01 % (sample ~ 10 g)

<b>Metrological parameters</b>	
Moisture content readability	0.0001 %
Drying temperature range	Max 250 °C
<b>Physical parameters</b>	
Leveling system	manual
Display	7" graphic colour touchscreen
Weighing chamber	automatic
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions W x D x H	476x381x346 mm
Net weight	5.3 kg
Gross weight	6.8 kg
<b>Construction</b>	
Protection class	IP 43
<b>Components and software</b>	
Database capacity	Products, Users, Packaging, Customers, Drying programs, Drying process reports, Ambient Conditions, Weighings
<b>Features of use</b>	
Display mode	%D, %M, %R, g
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
<b>Communication interface</b>	
Communication interface	RS232 <sup>1</sup> , USB-A, USB-B, Ethernet, Wi-Fi
<b>Electrical parameters</b>	
Power supply	100 – 120 V AC 50/60 Hz or 200-240 V AC 50/60 Hz
Power consumption	6 W
Heating module power	450 W
<b>Environmental conditions</b>	
Operating temperature	+10 – +40 °C
Mass indication control	External mass standard 50g, 100g, 200g, depending on the type of moisture analyzer (additional equipment)
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (additional equipment: GT105k-12/Z Control Thermometer)
<b>SOP – metrological tests (additional options)</b>	
Drying temperature control	One- or two-point, depending on the drying profile (additional equipment: GT105k-12/Z Control Thermometer)
Moisture content indication control	Certified MV Test Set (additional equipment)

<sup>1</sup> Barcode scanners, available as weighing instrument accessory, communicate with the instrument via RS232 interface exclusively.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

Antivibration Tables  
Moisture analyzer accessories  
Barcode scanners  
Protective cover for balances  
Receipt Printer

RS 232, RS 485 cables  
Additional modules  
RS 232 cables (scale - printer)  
RS 232 – RS 485 Converter

## Software (Additional Fee)

- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- RADWAG Development Studio [WX-010-0104]
- E2R Moisture Analyzers [WX-010-0072]
- Scale Editor 2.1 [WX-010-0173]

## Device dimensions W x D x H

