



More information on the website
radwag.com/en/info,w1,9DC

DWM 6000/HPS Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	6000 g
Minimum load	100 g
Readability [d]	2 g
Tare range	-6000 g
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 65
Construction	Stainless steel AISI304
Max. dimensions of sorted product [length × width]	500×280 mm
Weighing module	electromagnetic weighing module
Conveyors	belt
Pneumatic connector	6 bar, złącze samozaciskowe na przewód 12mm

Communication interface	
Communication interface	Ethernet, USB, RS232, I / O
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Features of use	
Conveyor velocity	1 m/s
Number of separators	6 or 12



Extra payment for verification

Accessories

RS 232 cables (scale - ZEBRA printer)
Barcode scanners
RS 232, RS 485 cables

Receipt Printer
USB cable (scale - printer)

Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]