



More information on the website
radwag.com/en/info,w1,9F9

DWT/HL 3000 HP Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	3000 g
Readability [d]	1 g
Tare range	-3000 g
Physical parameters	
Display	5.7" resistive colour touchscreen
Environmental conditions	
Operating temperature	0 ÷ +40 °C
Features of use	
Capacity	max 180 pcs/min
Speed	0.1-1 m/s



Extra payment for verification

Accessories

Displays
Transponder card readers
RS 232 cables (scale - ZEBRA printer)
Barcode scanners
Label Printers

RS 232, RS 485 cables
Keypad, external switches
USB adapter
Receipt Printer
USB cable (scale - printer)

Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]