



More information on the website
radwag.com/us/info,w1,A6P

CY10.60/120.C2.K Precision Balance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	60/120 kg
Minimum load	-
Readability [d]	1/2 g

Verification unit [e]	-
Tare range	-120 kg
Repeatability	2 g
Linearity	±2 g
Stabilization time	3 s
Adjustment	external
OIML Class	-
Physical parameters	
Leveling system	manualny
Display	10" graphic colour touchscreen
Weighing pan dimensions	400×500 mm
Packaging dimensions	720×620×210 mm
Net weight	13,5 kg
Gross weight	16 kg
Cable length	2,5 m
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	12÷15V DC
Power consumption	1A
Operating temperature	+15 ÷ +30 °C
Storage temperature	-25 ÷ +70 °C
Relative humidity	10% ÷ 80% RH no condensation

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

MediaBox
Mild steel powder coated weighing platforms
RFID Tags
Power Adapters
Additional Weighing platforms Module
Mild steel powder coated weighing platforms
Additional modules
Platforms in plastic casing
Professional Weighing Tables

Protective cover for balances
Barcode scanners
RS 232, RS 485 cables
Label Printers
RS 232, RS 485 cables
Fingerprint Reader
RS 232 – USB Converter
Receipt Printer

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

