



More information on the website  
[radwag.com/ja/info,w1,A73](http://radwag.com/ja/info,w1,A73)

# AS 120.X7

WL-113-0002



The drawings, photos and graphics used are for illustrative purposes only.



Autotest



Dosing



Plus/Minus Control



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit measurement



Statistics



Checkweighing



IR sensors



Under-pan weighing



GLP Procedures



Animal weighing



Density determination



Ambient conditions monitoring



Replaceable unit



Statistical Quality Control



ALIBI Memory



Mass for titrator



Wi-Fi



XXXXXXXX

XXXXXXXX [Max]

120 g

XXXX

1 mg

<b>Ważności</b>	
Waga [d]	0,01 mg
Waga [e]	1 mg
Waga	-120 g
Waga [5% Max]	0,01 mg
Waga [Max]	0,025 mg
Waga (USP)	20 mg
Waga (U=1%, k=2)	2 mg
Waga [5% Max]	0,02 mg
Waga [Max]	0,04 mg
Waga	±0,07 mg
Waga	2 s
Waga	Waga (Waga)
OIML	I
<b>Ważności</b>	
Waga	- LevelSENSING
Waga	7" Waga + Waga Waga
Waga	7Waga
Waga	, , , , , ,
Waga	190×190×222 mm
Waga	ø90 Waga + ø85 Waga mm
Waga	545×455×575 mm
Waga	7,3 kg
Waga	9,3 kg
<b>Waga</b>	
Waga	IP 43
<b>Waga</b>	
Waga	(Waga, Waga, Waga, Waga, Waga, Waga, Waga, Waga, Waga)
<b>Waga</b>	
Waga	Waga
<b>Waga</b>	
Waga	2×RS232 <sup>1</sup> , 2×USB-A Waga, USB-B, Wi-Fi, Ethernet
<b>Waga</b>	
Waga	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A : 12 – 15V DC 0,8A max
Waga max.	4 W
<b>Waga</b>	
Waga	+10 – +40 °C
Waga - Waga Waga	THBR 2.0 System, THBR BOX, THB P, THB W, THB S
Waga	40% – 80%

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

