



More information on the website
radwag.com/en/info,w1,AOI

XA 21/52.5Y.M.A.P Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Automatic sliding door
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	21/52 g
Minimum load	0.1 mg

Metrological parameters	
Readability [d]	1/5 µg
Verification unit [e]	1 mg
Tare range	-52 g
Standard repeatability [5% Max]	1.5 µg
Standard repeatability [Max]	6 µg
Standard minimum weight (USP)	3 mg
Standard minimum weight (U=1%, k=2)	0.3 mg
Permissible repeatability [5% Max]	2.4 µg
Permissible repeatability [Max]	8 µg
Linearity	±20 µg
Eccentric load deviation	20 µg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	~3.5 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatyczny - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, weighing pan, weighing pan shield, power supply, automatic pipette calibration adapter: (base, bottom ring, glass vessel, pipette calibration adapter, evaporation ring, weighing pan, glass lid, mechanical closing cover, protecting screw), brush, fabric dust cover.
Weighing chamber dimensions	199×170×217 mm
Capacity	11 ml
Weighing pan dimensions	ø26 mm
Packaging dimensions	750×492×595 mm
Net weight	14.5 kg
Gross weight	18.9 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.4A max*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration Tables
Power Adapters
Protective cover for balances
Additional modules
Anti-Draft Chamber for Microbalances
Automatic Variable-Volume Pipettes
Professional Weighing Tables
Protective cover for balances
Barcode scanners

Workstation for Pipettes Calibration
RS 232, RS 485 cables
Label Printers
THBR 2.0 System - Ambient Conditions Monitoring
RS 232, RS 485 cables
Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Antistatic ionizer
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Under-pan weighing

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- R-Pipettes [WX-010-0026]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]