






















More information on the website  
[radwag.com/us/info,w1,ASC](http://radwag.com/us/info,w1,ASC)

# XA 110.5Y.F Analytical Balance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Air density correction
-  Differential weighing
-  Ambient conditions monitoring
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

Maximum capacity [Max]	110 g
Minimum load	1 mg
Readability [d]	0,01 mg
Verification unit [e]	1 mg

Tare range	-110 mg
Standard repeatability [5% Max]	0,007 mg
Standard repeatability [Max]	0,02 mg
Standard minimum weight (USP)	14 mg
Standard minimum weight (U=1%, k=2)	1,4 mg
Permissible repeatability [5% Max]	0,01 mg
Permissible repeatability [Max]	0,03 mg
Linearity	±0,06 mg
Eccentric load deviation	0,06 mg
Sensitivity offset	$2 \times 10^{-6} \times Rt$
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times Rt$
Stabilization time	5 s (30 s for filters)
Adjustment	internal (automatic)
OIML Class	I
Sensitivity temperature drift	$1 \times 10^{-6} / ^\circ\text{C} \times Rt$
<b>Physical parameters</b>	
Leveling system	semi-automatic – LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber doors	manual
Delivery components	Analytical Balance, weighing pan, weighing pan for filters, weighing pan shield, centring ring, bottom cover, brush, fabric dust cover, power supply.
Weighing pan dimensions	210×254 mm for filters + ø90 mm open-work pan + ø85 mm standard pan (option)
Packaging dimensions	865×510×690 mm
Net weight	12,7 kg
Gross weight	25 kg
<b>Construction</b>	
Protection class	IP 43
<b>Communication interface</b>	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
<b>Power supply</b>	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,1A max
<b>Operating temperature</b>	
Operating temperature	+10 – +50 °C

**Repeatability** is expressed as a standard deviation from 10 weighing cycles.

**Stabilization time** depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

MediaBox  
RFID Tags  
Antivibration tables  
Power Adapters  
RS 232, RS 485 cables  
Density determination KIT  
Additional modules  
Professional Weighing Tables  
Protective cover for balances  
Barcode scanners

Label Printers  
THBR 2.0 System - Ambient Conditions Monitoring  
RS 232, RS 485 cables  
Protective cover for balances  
Under-pan weighing  
Antistatic ionizer  
Receipt Printer  
Fingerprint Reader  
RS 232 – USB Converter  
Under-pan weighing

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

