



More information on the website
radwag.com/en/info,w1,AUZ

UMA 5.5Y Automatic Mass Comparator



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
E1 Calibration Range	1 mg ÷ 5 g
E2 Calibration Range	1 mg ÷ 5 g
F1 Calibration Range	1 mg ÷ 5 g
F2 Calibration Range	1 mg ÷ 5 g
Maximum capacity [Max]	6.1 g
Readability [d]	0.0001 mg
Standard repeatability [5% Max]	0.2 µg
Standard repeatability [Max]	0.4 µg
Permissible repeatability	0.6 µg
Eccentricity (tested load)	0 µg
Electric compensation range	0 ÷ 6.1 g
Stabilization time	30 s
Adjustment	internal (automatic)
Physical parameters	
Display	10" graphic colour touchscreen

Physical parameters	
Magazine positions	36
Weighing pan dimensions	ø20 mm
Weighing device dimensions	950×590×540 mm
Controlling device dimensions	460×250×195 mm
Packaging dimensions	1200×800×1281 mm
Net weight	102.5 kg
Gross weight	183.5 kg
Supplementary weights internal	-
Supplementary weights external	-

Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot

Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz

Environmental conditions	
Operating temperature	+15 ÷ +30 °C
Operating temperature change rate	±0.5°C/12h (±0.3°C/4h)
Relative humidity	40% ÷ 60%
Relative humidity change rate	±5%/12h (3%/4h)

Repeatability is expressed as a standard deviation determined for 6 ABBA cycles. Standard deviation is experimentally determined under ambient conditions for calibration of E1 class mass standards specified in OIML R111 (Table C.1.) document.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories

RFID Tags
 Antivibration Tables
 Additional modules
 Protective cover for balances
 Barcode scanners
 RS 232, RS 485 cables

THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 RS 232, RS 485 cables
 RS 232 cables (scale - printer)

Software

- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]

- RMCS Lite [WX-010-0164]

Device dimensions



UMA-100, UMA-1000



UMA-control unit



UMA-5

