



More information on the website
radwag.com/us/info,w1,AYW

MA 110.R.NS Moisture Analyzer



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Autotest



Statistics



GLP Procedures



Replaceable unit



Statistical Quality Control



ALIBI Memory



Drying modes



Samples drying



Moisture content analysis



Dry mass determination

Datasheet

Maximum capacity [Max]	110 g
Readability [d]	1 mg
Tare range	-110 g
Adjustment	external
Maximum sample weight	110 g
Heating module	metal heater
Moisture content repeatability	+/-0,05% (sample ~ 2g), +/-0,01% (sample ~ 10g)
Moisture content readability	0,001%

Drying temperature range	Max 160 °C
Physical parameters	
Leveling system	manualny
Display	LCD (backlit)
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions	476×381×346 mm
Net weight	4,8 kg
Gross weight	6,3 kg
Construction	
Protection class	IP 43
Features of use	
Display mode	%MC, %DC, %ATRO MC, %ATRO DC, g, g/kg MC, g/kg DC, -%MC
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
Communication interface	
Communication interface	RS232 ¹ , USB-A, USB-B, Wi-Fi
Power supply	
Power supply	100V – 120V AC 50/60Hz or 200V-240V AC 50/60Hz
Power consumption	4 W
Heating module power	450 W
Operating temperature	
Operating temperature	+10 ÷ +40 °C
Mass indication control	
Mass indication control	External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer)
Internal adjustment	For .IC models only, GLP report
External adjustment	For all models, GLP report
Drying temperature control	One- or two-point, depending on the drying profile (equipment: GT105k-12/Z Control Thermometer)
Moisture content indication control	Certified MV Test Set
Internal / External adjustment	
Internal / External adjustment	Depending on the type of moisture analyzer, GLP report
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (equipment: GT105k-12/Z Control Thermometer)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

Antivibration tables
Moisture analyzer accessories

Receipt Printer
RS 232, RS 485 cables

Software

• RAD Key [WX-010-0005]

• RADWAG Development Studio [WX-010-0104]

Device dimensions

