



More information on the website  
[radwag.com/us/info,w1,AZ3](http://radwag.com/us/info,w1,AZ3)

# MYA 11/52.5Y Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

Maximum capacity [Max]	11/52 g
Minimum load	0,1 mg
Readability [d]	1/10 µg

Verification unit [e]	1 mg
Tare range	-52 g
Standard repeatability [5% Max]	1,5 µg
Standard repeatability [Max]	10 µg
Standard minimum weight (USP)	3 mg
Standard minimum weight (U=1%, k=2)	0,3 mg
Permissible repeatability [5% Max]	2,7 µg
Permissible repeatability [Max]	15 µg
Linearity	±10/30 µg
Eccentric load deviation	6/10 µg
Sensitivity time drift	1×10 <sup>-6</sup> /Year×Rt
Stabilization time	3,5 s
Adjustment	internal (automatic)
OIML Class	I
<b>Physical parameters</b>	
Leveling system	automatyczny - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø90×90 mm
Weighing pan dimensions	ø26 + ø40 mm
Packaging dimensions	750×492×595 mm
Net weight	10 kg
Gross weight	16,6 kg
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

MediaBox  
RFID Tags  
Antivibration tables

RS 232, RS 485 cables  
THBR 2.0 System - Ambient Conditions Monitoring  
RS 232, RS 485 cables

Power Adapters  
Additional modules  
Anti-Draft Chamber for Microbalances  
Professional Weighing Tables  
Antistatic ionizer  
Protective cover for balances  
Barcode scanners

Chamber for filter weighing  
Weighing dishes  
Receipt Printer  
Fingerprint Reader  
Protective cover for balances  
RS 232 – USB Converter

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

